

[See all 33 Products in Family](#)

## 10 x 10mm, 500µm Pitch, 2.2° Divergence, Cyl. Microlens Array



Stock #86-842 **11 In Stock**

A\$1,318<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	A\$1,318.00 each
Qty 11-25	A\$1,160.00 each
Qty 26-49	A\$1,095.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Lens Array Type:

### Physical & Mechanical Properties

10.0 x 10.0 ±0.05 Dimensions (mm):

3.000 Radius R (mm):

1.20 ±0.05 **Thickness (mm):**

## Optical Properties

6.60 **Effective Focal Length EFL (mm):**

[Fused Silica](#) (Corning 7980) **Substrate:**

Uncoated **Coating:**

200 - 2200 **Wavelength Range (nm):**

±2.2 **Divergence Angle (°):**

500.00 ±0.25 **Pitch (µm):**

Single-Sided **Array Type:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

## Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.