

TECHSPEC<sup>®</sup> 10 x 10mm Protected Gold Coated, *N*/10 ZERODUR<sup>®</sup> Mirror

See More by [SCHOTT Optical Components](#)



Stock **#39-861** **2 In Stock**

-

1

+

A\$203<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | A\$203.20 each                |
| Qty 6-25       | A\$161.60 each                |
| Qty 26-49      | A\$152.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                  |
|----------------------------------|------------------|
| Flat Mirror                      | Type:            |
| Physical & Mechanical Properties |                  |
| Commercial Polish                | Back Surface:    |
| 10.0 x 10.0 +0.00/-0.20          | Dimensions (mm): |

|                      |                       |
|----------------------|-----------------------|
| Protective as needed | Bevel:                |
| 90                   | Clear Aperture (%):   |
|                      |                       |
| Ground               | Edges:                |
| 30                   | Parallelism (arcsec): |
|                      |                       |
| 2.00 ±0.20           | Thickness (mm):       |
|                      |                       |
| 10.00                | Length (mm):          |
|                      |                       |
| 10.00                | Width (mm):           |

Optical Properties

|                                                                                 |                                |
|---------------------------------------------------------------------------------|--------------------------------|
| λ/10                                                                            | Surface Flatness (P-V):        |
|                                                                                 |                                |
| ZERODUR®                                                                        | Substrate: □                   |
|                                                                                 |                                |
| 20-10                                                                           | Surface Quality:               |
|                                                                                 |                                |
| R <sub>avg</sub> >96% @ 700 - 2000nm<br>R <sub>avg</sub> >96% @ 2000 - 10,000nm | Coating Specification:         |
|                                                                                 |                                |
| Protected Gold (700-10000nm)                                                    | Coating:                       |
|                                                                                 |                                |
| Metal                                                                           | Coating Type:                  |
|                                                                                 |                                |
| 700 - 10000                                                                     | Wavelength Range (nm):         |
|                                                                                 |                                |
| 0.8 J/cm <sup>2</sup> @ 1064nm, 10ns                                            | Damage Threshold, Reference: □ |

Material Properties

|     |                                                              |
|-----|--------------------------------------------------------------|
| 0.1 | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
|-----|--------------------------------------------------------------|

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
|           |                             |
| View      | Certificate of Conformance: |
|           |                             |
| Compliant | Reach 247:                  |

## Product Details

- Precision ZERODUR® Substrates
- λ/10 Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR® λ/10 First Surface Mirrors are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of ±0.10 x 10<sup>-6</sup>/°C, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR® λ/10 First Surface Mirrors feature precision polished substrates with λ/10 flatness and 20-10 surface quality. Multiple metallic and enhanced metallic coating options are available, allowing for these mirrors to be easily integrated into applications in both the visible and infrared spectrum.

**Note:** Surface flatness is measured before coating.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts