

TECHSPEC® 100mm Dia., 0.33 Numerical Aperture NIR Coated, Aspheric Lens



Stock #22-717 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$1,680.00

ADD TO CART

Qty 1-5
A\$1,680.00
Qty 6+
A\$1,344.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
100.00 +0.0/-0.1

Effective Focal Length EFL (mm):
150.00 @ 587.6nm

Numerical Aperture NA:
0.33

Back Focal Length BFL (mm): 135.50
Substrate: N-BK7
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 90
Edge Thickness ET (mm): 5.11
Center Thickness CT (mm): 22.00 ±0.1
f#: 1.50
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 6.67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant