


[See all 13 Products in Family](#)

100 x 100mm, 0.7mm Thick, EAGLE XG® Window



Stock #18-297 **20+ In Stock**

- 1 + A\$80^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$80.00 each
Qty 6-25	A\$64.00 each
Qty 26-99	A\$59.20 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**
Glass **Type of Window:**

Physical & Mechanical Properties

90.00 x 90.00 **Clear Aperture CA (mm):**

100.00 x 100.00 ±0.25	Dimensions (mm):
0.70 ±0.07	Thickness (mm):
100.00	Length (mm):
100.00	Width (mm):
Protective as needed	Bevel:
90	Clear Aperture (%):
Cut and Seamed	Edges:
0.23	Poisson's Ratio:
73.6	Young's Modulus (GPa):

Optical Properties

Uncoated	Coating:
EAGLE XG®	Substrate: <input type="checkbox"/>
1.51	Index of Refraction (n_d):
80-50	Surface Quality:
350 - 2000	Wavelength Range (nm):

Material Properties

2.38	Density (g/cm³):
3.17 (0 to +300°C)	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Thin 0.7mm EAGLE XG® Substrates
- High Chemical Resistance and Excellent Durability
- Low Density for Weight Sensitive Applications

EAGLE XG® Windows are constructed from heavy-metal free glass through a fusion drawn process, providing these windows with exceptionally smooth, flat surfaces. These windows have high transmission in the visible spectrum, excellent environmental durability, and high chemical resistance. The low density of Corning® EAGLE XG® coupled with the thinness of these windows makes them ideal for weight and space sensitive applications. EAGLE XG® Windows are used as substrates for mobile device LCDs, substrates for polarizers, wafers for semiconductor applications, or protective windows for electronic displays.

Technical Information

EAGLE XG® Typical Transmission



Quote Your Size
