

TECHSPEC® 100 x 100mm UV-Enhanced Aluminum Coated, λ/10 ZERODUR® Mirror



TECHSPEC ZERODUR λ/10 First Surface Mirrors

Stock **#17-806** 3-5 DAYS

- 1 + **A\$865.60**

ADD TO CART

Qty 1-5

A\$865.60

Qty 6+

A\$692.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: ☐
[ZERODUR®](#)

Back Surface:
Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 100.0 x 100.0 +0.00/-0.20
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 10.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 250 - 700
Length (mm): 100.00
Width (mm): 100.00
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.5 J/cm ² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant