

**TECHSPEC® 600 x 1000mm Linear Polarizing Film (XP42-18)**



Stock #86-185 CLEARANCE **20+ In Stock**

-
1
+
A\$404<sup>.72</sup>

ADD TO CART

Volume Pricing	
Qty 1+	<b>A\$404.72</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

**Note:**  
Polarization axis can be identified as follows:  
Circular Parts - Parallel to direction of notch on polarizer  
Square Parts - Parallel to mark on protective film  
Rectangular Parts - Parallel to first listed dimension

**Physical & Mechanical Properties**

**Dimensions (mm):**  
600.0 x 1000.0 +5.0/0.0

0.19 ±0.03

Thickness (mm):

Polarizing Film

Construction:

## Optical Properties

9000:1 (nominal at 555nm)

Extinction Ratio:

[Polymer Film XP42-18](#)

Substrate: □

Single: 42

Parallel: 36

Crossed: <0.004 (nominal at 555nm)

Transmission (%):

400 - 700

Wavelength Range (nm):

>99.98 (nominal at 555nm)

Polarization Efficiency (%):

## Environmental & Durability Factors

-40 to +80

Operating Temperature (°C):

80 x 500

Heat Resistance (°C x Hours):

## Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

Reach 235:

## Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available

Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

**Note:** Polarizer Film with adhesive available.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

## Technical Information

