

TECHSPEC<sup>®</sup> 101.6 x 516.8mm EFL 15° Bare Gold 100Å Off-Axis Parabolic Mirror



Stock #35-667 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$1,488.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| A\$1,488.00                   |
| Qty 6+                        |
| A\$1,339.20                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Type:  
Off-Axis Parabolic Mirror

Diameter (mm):  
101.60 +0.00/-0.38

Effective Focal Length EFL (mm):  
516.81

|                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                                  |
| <b>Radius of Curvature (mm):</b><br>1,016.00                                                                                                              |
| <b>Coating:</b><br>Bare Gold                                                                                                                              |
| <b>Coating Type:</b><br>Metal                                                                                                                             |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥94% @ 700 - 800nm<br>R <sub>avg</sub> ≥97% @ 800 - 2,000nm<br>R <sub>avg</sub> ≥98% @ 2,000 - 12,000nm |
| <b>Off-Set Angle (°):</b><br>15                                                                                                                           |
| <b>Parent Focal Length PFL (mm):</b><br>508.00                                                                                                            |
| <b>Surface Figure, RMS:</b><br>1λ                                                                                                                         |
| <b>Surface Roughness (Angstroms):</b><br><100 RMS                                                                                                         |
| <b>Wavelength Range (nm):</b><br>700 - 12000                                                                                                              |
| <b>Clear Aperture (%):</b><br>90                                                                                                                          |
| <b>Surface Quality:</b><br>80-50                                                                                                                          |
| <b>Compatible Mounting Plates:</b><br><a href="#">#83-977</a>                                                                                             |
| <b>Substrate:</b><br>Aluminum 6061-T6                                                                                                                     |
| <b>Y Offset (mm):</b><br>133.75                                                                                                                           |
| <b>Reflected Wavefront, RMS:</b><br>2λ                                                                                                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |