

**TECHSPEC® 100mm Length, T-Mount Extension Tube**



Stock **#65-969** **3 In Stock**

⊖ 1 ⊕ **A\$154<sup>00</sup>**

**ADD TO CART**

Volume Pricing

Qty 1-4	<b>A\$154.40</b> each
Qty 5-9	<b>A\$137.12</b> each
Qty 10-25	<b>A\$127.04</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Extension Tube **Type:**

Extension Tube (Fixed) **Function:**

**Note:**  
Inner threads are female T-Mount (M42 x0.75), allowing optical components to be mounted with [#58-741](#)

## Physical & Mechanical Properties

100.0      **Extension Length (mm):**

103.45      **Total Length (mm):**

37.0      **Clear Aperture CA (mm):**

48.0      **Outer Diameter (mm):**

## Threading & Mounting

T-Mount      **Thread Type:**

## Regulatory Compliance

[Compliant](#)      **RoHS 2015:**

[View](#)      **Certificate of Conformance:**

[Compliant](#)      **REACH 241:**

## Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.