

10.4" Diameter, 8.0" FL, Aspheric Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock #32-595 3-5 DAYS



1



A\$208.00

ADD TO CART

Qty 1-10

A\$208.00

Qty 11+

A\$181.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):

264.16

Effective Focal Length EFL (mm):

203.20

Substrate: ☐

Acrylic

Coating:

Uncoated
Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Diameter (inches): 10.4
Dimensional Tolerance (inches): ±0.05
Effective Diameter (inches): 10.0
Effective Focal Length EFL (inches): 8.00
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)
Typical Applications: Designed for finite conjugates of 4f (grooved side) and 4/3*f (flat side)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View