

[See all 10 Products in Family](#)

## 100mW, 808nm Fiber-Coupled Laser Module



Stock #19-485 **2 In Stock**

⊖ 1 ⊕ A\$1,392<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	A\$1,392.00 each
Qty 10+	A\$1,252.80 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads



### General

Type of Laser:  
Diode

Laser Class - CDRH:  
Class IIIb

### Physical & Mechanical Properties

Length of Fiber (m):  
1

151.00 Length (mm):

## Optical Properties

Fiber-Coupled Spatial Mode:

808.00 ±5 Wavelength (nm):

Infrared Color:

## Electrical

100 Output Power (mW):

## Hardware & Interface Connectivity

5.0 Operating Voltage (V):

Fiber-Coupled Output Type:

SMA Connector:

## Environmental & Durability Factors

+15 to +30 Operating Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 233:

## Product Details

- 400µm Core Multimode Fiber with SMA Connector
- 50 and 100mW Output Power Options
- VIS and NIR Wavelengths Available
- [Free Space Alignment Lasers](#) Also Available

Fiber-Coupled Laser Modules feature an integrated 1m long, 400µm core fiber with an SMA905 connector. These cost-effective lasers provide up to 100mW of output power and have a long expected lifetime of 5000 hours. Fiber-Coupled Laser Modules are ideal for use in laser alignment, laser pointing, and laser measurement applications where a free-spaced laser diode module may be difficult to position. These lasers' compact size and easy operation make them well suited for integration into OEM systems.

**Note:** Power supply is sold separately.