

TECHSPEC® 101.6 x 101.6mm, Enhanced Aluminum, 4-6λ Mirror



Stock #18-926 3-5 DAYS

-

1

+

A\$86.40

ADD TO CART

Qty 1-5

A\$86.40

Qty 6+

A\$68.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):
101.60 x 101.60 +0.00/-0.25

Coating Specification: R_{avg} ≥95% @ 450 - 650nm @ 45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 91.44 x91.44
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 (nominal)
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 101.60
Width (mm): 101.60
Damage Threshold, By Design: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant