


[See all 32 Products in Family](#)

1064nm, 18-23mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_1064_Q-20

See More by [AdlOptica](#)



Focal Flat Top Beam Shaper



Stock #12-237 **1 In Stock**

-

1

+

A\$5,055⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$5,055.00 each
Qty 5-10	A\$4,544.00 each
Qty 11+	A\$4,299.00 each
Need More?	Request Quote

Product Downloads

General

πShaper_1064_Q-20

Model Number:

Type:

Beam Shaper	
Compatible Adapter:	
#12-323	
Physical & Mechanical Properties	
Length (mm):	
21.00	
Weight (g):	
70	
Clear Aperture CA (mm):	
38	
Diameter (mm):	
64.00	
Input Beam Diameter, 1/e ² (mm):	
18 - 23	
Optical Properties	
Transmission (%):	
>99	
Design Wavelength DWL (nm):	
1064	
Wavelength Range (nm):	
1020 - 1100	
Input Beam Mode:	
TEM ₀₀	
Typical Input Beam Mode Quality, M ² :	
<1.5	
Input Beam Divergence (mrad):	
±20	
Electrical	
Maximum Input Power, CW (kW):	
0.4	
Threading & Mounting	
Inner Thread:	
M58 x 1	
Outer Thread:	
M58 x 1	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 250:	
Compliant	

Product Details

- Shapes Gaussian Beams to AiryDisk Profile
 - AiryDisk is Focusable to Flat Top Spot
 - Near 100% Efficiency
 - [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available
- AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

