

1070nm Dual Stage Free-Space Optical Isolator



1070nm Dual Stage Free-Space Optical Isolator, #35-988

Stock **#35-988** 3-5 DAYS

⊖ 1 ⊕

A\$7,451.20

ADD TO CART

Qty 1+
A\$7,451.20
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 4.7
Design Wavelength DWL (nm): 1070
Minimum Transmission (%): 80
Operating Temperature (°C): +15 to +40
Transmission (%): 90 (typical)

Type: Dual Stage Optical Isolator
Wavelength Range (nm): 1050 - 1100
Style: Faraday
Damage Threshold, By Design: ☐ 40 W, 4 kW/cm ² @ DVL
Typical Isolation at Design Wavelength (dB): 67
Minimum Isolation at Design Wavelength (dB): 60

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
