

TECHSPEC[®] 10mm 632.8nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#47-777** 20+ In Stock

-

1

+

A\$438⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$438.40 each
Qty 6-25	A\$355.20 each
Qty 26-99	A\$321.60 each
Need More?	Request Quote

Product Downloads

General	
Linear Polarizer	Type:
Physical & Mechanical Properties	
Protective as needed	Bevel:
90.00	Clear Aperture (%):

Cube	Construction:
10.0 x 10.0 x 10.0 ±0.1	Dimensions (mm):
Optical Properties	
±3	Beam Deviation (arcmin):
R _{abs} <0.25% @ 632.8nm	Coating Specification:
632.8	Design Wavelength DWL (nm):
1000:1	Extinction Ratio:
>95	P-Polarization Transmission (%):
>99.5	S-Polarization Reflection (%):
N-BK7	Substrate: ☐
40-20	Surface Quality:
1.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

Product Details

- Designed for Common Diode, Gas, and Solid State Lasers
- Reflects S-Polarized Light, Transmits P-Polarized Light
- High Extinction Ratio

TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision [right angle prisms](#) cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.

LASER OPTICS

MADE BY EDMUND OPTICS®

LEARN MORE

Technical Information