

TECHSPEC®

10mm Dia., 0.50 Numerical Aperture, 900-1700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-991-INK** 10-15 DAYS

[Other Coating Options](#)



1



A\$400.00

ADD TO CART

Qty 1-5

A\$400.00

Qty 6+

A\$320.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
10.00 ±0.025

Effective Focal Length EFL (mm):
10.00 @ 587.6nm

Numerical Aperture NA: 0.50
Back Focal Length BFL (mm): 5.68
Substrate: ☐ N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: SWIR+ (900-1700nm)
Coating Specification: R _{avg} <0.5% @ 900 - 1700nm @ ±30° AOI R _{abs} <1.5% @ 900 - 1700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 9.00
Edge Thickness ET (mm): 6.18
Center Thickness CT (mm): 7.80 ±0.10
f#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 900 - 1700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View