

[See all 16 Products in Family](#)

**TECHSPEC® 10mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror**



Nd:YAG ZERODUR Laser Line Mirrors

Stock **#26-414** **12 In Stock**

⊖ 1 ⊕ **A\$307<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>A\$307.20</b> each
Qty 6-25	<b>A\$281.60</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

2.00 +/-0.2 **Thickness (mm):**

10.00 +0.00/-0.20 **Diameter (mm):**

**Clear Aperture (%):**

>90

Parallelism (arcsec):

30

## Optical Properties

Substrate:

ZERODUR®

Surface Quality:

20-10

Angle of Incidence (°):

45

Coating:

Laser Mirror (355nm)

Design Wavelength DWL (nm):

355

Reflection at DWL (%):

99.8

Wavelength Range (nm):

351 - 358

Surface Flatness (P-V):

$\lambda/10$

Coating Specification:

$R_{\text{abs}} > 99.8\%$  @ 355nm @ 45° AOI  $R_{\text{avg}} > 99.5\%$  @ 351 - 358nm @ 45° AOI

Coating Type:

Dielectric

Damage Threshold, By Design:

6 J/cm<sup>2</sup> @ 355nm, 20ns, 20Hz

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.5% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Nd:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Nd:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of  $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$  these mirrors are ideal for applications where the optics will be exposed to fluctuating temperatures. The Nd:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Nd:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with  $\lambda/10$  flatness and 20-10 surface quality. These mirror are an excellent fit for laboratories and integration into larger powerful laser systems