

10mm Dia. x 10mm EFL Arton Plastic Asphere, Coated



Stock #90-323 3-5 DAYS

- 1 +

A\$92.80

ADD TO CART

Qty 1-10
A\$92.80
Qty 11+
A\$76.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
10.00

Effective Focal Length EFL (mm):
10.00 ±0.2

Numerical Aperture NA:
0.40

Back Focal Length BFL (mm):
8.28

Substrate: Arton Plastic
Coating: BBAR (650-850nm)
Coating Specification: R _{abs} <1.0% @ 650 - 850nm
Clear Aperture CA (mm): 8.00
Edge Thickness ET (mm): 3.1
f/#: 1.25
Bevel: Protective bevel as needed
Flange Distance (mm): 8.28
Type: Aspheric Lens
Wavelength Range (nm): 650 - 850
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View