

TECHSPEC[®] 10mm Dia. x 30mm FL, Uncoated, Double-Convex Lens



Stock **#63-539** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$47.20

ADD TO CART

Qty 1-9
A\$47.20
Qty 10+
A\$42.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Back Focal Length BFL (mm):
29.17

Effective Focal Length EFL (mm): 30.00
Coating: Uncoated
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.68
Radius R₁=R₂ (mm): 30.58
Clear Aperture CA (mm): 9.00
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant