

[See all 2 Products in Family](#)

## TECHSPEC® 10mm Schmidt-Pechan Prism



TECHSPEC® Pechan Prism

Stock **#36-038** **20+ In Stock**

⊖ 1 ⊕ A\$718<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	A\$718.40 each
Qty 6-25	A\$574.40 each
Qty 26-99	A\$537.60 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Schmidt-Pechan Prism **Type:**

### Physical & Mechanical Properties

20.2 **Height (mm):**

12.99 **Thickness (mm):**

±0.1 Dimensional Tolerance (mm):

14.00 Width (mm):

## Optical Properties

Coating: VS 0° & Aluminized

Substrate:  N-BK7

Surface Quality: 40-20

Image Orientation: Right-Handed

Coating Specification: Entrance/Exit Faces:  $R_{avg} \leq 0.4\%$  @ 425 - 675nm  
Roof:  $R_{avg} > 85\%$  @ 400 - 700nm w/Black Overpaint

Ray Deviation (°): 0

Wavelength Range (nm): 400 - 700

Ray Deviation Tolerance (arcmin): ±10

Power (fringes) @ 632.8nm: 1.00

Irregularity (fringes) @ 632.8nm: 0.25

## Regulatory Compliance


Certificate of Conformance: [View](#)

## Product Details


- Provides Inline Image Rotation of 180°
- Compact Design for OEM Integration
- Air Spaced for Optimal Performance

TECHSPEC® Schmidt-Pechan Prisms leverage Edmund Optics' manufacturing expertise to deliver a precision inline instrumentation prism to rotate an image by 180 degrees. This image rotation is employed in many direct view applications and replaces a relay prism or lens system for a more compact optical train. Overall clarity of the system is ensured by adding both an anti-reflective and metallic coating to each prism. The TECHSPEC® Schmidt-Pechan Prisms feature 5 arcsecond roof angle tolerances to maintain image resolution.


## Technical Information



#36-038



Schmidt-Pechan Prism Ray Path



*Schmidt-Pechan Prism Tunnel Diagram*

;