

[See all 14 Products in Family](#)

10mW, 405nm Violet Alignment Laser Diode Module



Violet Alignment Laser Diode

Stock **#37-025** **9 In Stock**

-

1

+

A\$528⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$528.00 each
Qty 10+	A\$475.20 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



SPECIFICATIONS

General

IIIbLaser Class - CDRH:

Physical & Mechanical Properties

36.00	Length (mm):
Optical Properties	
405.00	Wavelength (nm):
±5	Wavelength Tolerance (nm):
3.5 Typical	Beam Diameter (mm):
<0.5	Beam Divergence (mrad):
Violet	Color:
Electrical	
10	Output Power (mW):
0 - 10	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
5	Operating Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #73-818 Europe: #73-818 Japan: #13-640 Korea: #33-770 China: #73-818	
Environmental & Durability Factors	
15 to 30	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- TTL Modulation up to 10kHz
- Circular and Elliptical Beam Profiles
- Focus Adjustable

Violet and Blue Alignment Laser Diodes are ideal for alignment and sensing applications. Available with output power options ranging from 1 to 100mW, these lasers are commonly integrated into visual-based systems or monochromatic vision systems. Because monochromatic vision systems are typically illuminated with green or red lights, a 405 or 450nm alignment laser can be easily filtered out without affecting the system's illumination. These lasers feature simple operation due to the integrated optics and electronics and are easily powered via a 5VDC source. Violet and Blue Alignment Laser Diodes feature an external focusing mechanism and accept interchangeable projection heads.

Note: Power supply and mounting bracket sold separately.