

TECHSPEC® 10X, VIS-NIR Vega® Broadband Beam Expander



TECHSPEC® Vega™ Broadband Beam Expanders

Stock **#39-740** 3-5 DAYS

⊖ 1 ⊕ **A\$857.60**

ADD TO CART

Qty 1-9

A\$857.60

Qty 10+

A\$758.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser VIS-NIR (500-1090nm)

Design Wavelength DWL (nm):
Broadband

Entrance Aperture (mm): 5.45
Exit Aperture (mm): 25.5
Expansion Power: 10X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 90.80
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5
Transmission (%): >94.0 (nominal)
Type: Beam Expander
Weight (g): 167
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: λ/10 for 2.3mm input beam (nominal, λ = DWL)
Coating Specification: R _{avg} ≤ 1.5% @ 500 - 1090nm @ 0° AOI
Wavelength Range (nm): 500 - 1090
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 2 J/cm² @ 1064nm, 20ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View