


11 x 11mm, 1550nm, Corning Polarcor™ Glass Polarizer



Corning Polarcor™ Glass Polarizers

Stock #13-623 3-5 DAYS

⊖ 1 ⊕

A\$1,320.00

ADD TO CART

Qty 1+
A\$1,320.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0 ±5

Coating:
BBAR (1510-1590nm)

Design Wavelength DWL (nm):
1550

Extinction Ratio:
>100,000:1

Substrate: ☐

Borosilicate Glass Containing Elongated Silver Crystals	
Length (mm):	11.00
Minimum Transmission (%):	>98.5
Dimensions (mm):	11.0 x 11.0
Surface Quality:	40-20
Thickness (mm):	0.50 ±0.05
Dimensional Tolerance (mm):	±0.1
Coating Specification:	R _{avg} <0.25% @ 1510 - 1590nm
Wavelength Range (nm):	1510 - 1590
Width (mm):	11.00
Insertion Loss (dB):	<0.06
Index of Refraction n _d :	1.5051
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):	6.5
Knoop Hardness (kg/mm²):	480
Young's Modulus (GPa):	58.605
Poisson's Ratio:	0.21
Abbe Number (v _d):	57.6
Density (g/cm³):	2.412

Regulatory Compliance

RoHS 2015:	Compliant
Reach 224:	Compliant
Certificate of Conformance:	View