

TECHSPEC[®] 10mm Schmidt-Pechan Prism



TECHSPEC[®] Pechan Prism

Stock **#36-038** 3 In Stock

-

1

+

A\$718⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$718.40 each
Qty 6-25	A\$574.40 each
Qty 26-99	A\$537.60 each
Need More?	Request Quote

Product Downloads

General

Schmidt-Pechan Prism

Type:

Physical & Mechanical Properties

20.2

Height (mm):

12.99

Thickness (mm):


±0.1	Dimensional Tolerance (mm):
14.00	Width (mm):
Optical Properties	
VS 0° & Aluminized	Coating:
N-BK7	Substrate: ☐
40-20	Surface Quality:
Right-Handed	Image Orientation:
Coating Specification: Entrance/Exit Faces: R _{avg} ≤0.4% @ 425 - 675nm Roof: R _{avg} >85% @ 400 - 700nm w/Black Overpaint	
0	Ray Deviation (°):
400 - 700	Wavelength Range (nm):
±10	Ray Deviation Tolerance (arcmin):
1.00	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details


- Provides Inline Image Rotation of 180°
- Compact Design for OEM Integration
- Air Spaced for Optimal Performance

TECHSPEC® Schmidt-Pechan Prisms leverage Edmund Optics' manufacturing expertise to deliver a precision inline instrumentation prism to rotate an image by 180 degrees. This image rotation is employed in many direct view applications and replaces a relay prism or lens system for a more compact optical train. Overall clarity of the system is ensured by adding both an anti-reflective and metallic coating to each prism. The TECHSPEC® Schmidt-Pechan Prisms feature 5 arcsecond roof angle tolerances to maintain image resolution.


Technical Information



#36-038



Schmidt-Pechan Prism Ray Path



Schmidt-Pechan Prism Tunnel Diagram

