

[See all 6 Products in Family](#)

110mm Travel, Ultra Precision Linear Motor Stage, Integrated Controller, Linear Encoder

See More by [Zaber™](#)



Stock **#70-564** **2 In Stock**

-

1

+

A\$14,800⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$14,800.00 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Yes	Encoder:
Yes	Manual Control/ LED Indicators:
Zaber Technologies Inc.	Manufacturer:

Note:
Requires a 24-48 VDC power supply and either [#15-](#)

[295](#) for USB connectivity or [#15-297](#) for RS-232 connectivity. A data cable ([#15-296](#) or [#15-299](#)) can be used to daisy chain multiple stages together to control simultaneously.

Moving Magnet Track Linear Motor	Type of Motor:
Linear Analog Encoder	Encoder Type:

Physical & Mechanical Properties

Linear (X)	Type of Movement:
Crossed-Roller Bearing	Guide System:
245 x 151.5	Stage Size (mm):
110	Travel (mm):
1	Accuracy (µm):
44	Height (mm):
12	Load Capacity (kg):
<0.08	Repeatability (µm):
0.00061 - 1200	Speed (mm/s):
3.76	Weight (kg):

Electrical

3000	Maximum Operating Current (mA):
------	---------------------------------

Hardware & Interface Connectivity

Moving Magnet Track Linear Motor	Type of Drive:
Power Supply Required and Sold Separately: USA: #70-960 Europe: #70-960 Japan: #23-662 Korea: #33-773 China: #70-960	Power Supply:
RS-232	Computer Interface:

Environmental & Durability Factors

10 - 40	Operating Temperature (°C):
---------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- 60, 110, 210mm Travel Options
- Up to 1200mm/s Speed
- Ultra-High Repeatability and Accuracy

Zaber™ Ultra High Precision Linear Motorized Stages are computer-controlled linear stages that utilize a moving magnet track linear motor and centrally located encoder to accurately and precisely position optical components or subsystems. These stages can connect directly to a computer's USB or RS-232 port and are compatible with [Zaber Launcher](#) and [Zaber's Motion Library](#) for quick set up and intuitive automation and control. The linear analog encoder has 1nm count size ensuring 1µm positional accuracy, < 0.08µm repeatability, and consistent minimal incremental movement steps down to 20nm. Zaber™ Ultra High Precision Linear Motorized Stages are driven by non-cogging ironless linear motors which allow for speeds up to 1200mm/s with a minimum speed and speed resolution of 0.61mm/s. These stages are designed with metric tapped holes for mounting and an indexed knob and push switch for manual control when needed.