

TECHSPEC® 10mm Square Enhanced Aluminum Coated, λ/10 Mirror



Stock **#64-010** [CONTACT US](#)

- 1 + **A\$124.00**

ADD TO CART

Qty 1-5
A\$124.00
Qty 6+
A\$99.20
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: [Fused Silica](#) (Corning 7980)

Back Surface:
Commercial Polish

Surface Quality:

20-10
Dimensions (mm): 10.0 x 10.0
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 2.00 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Length (mm): 10.00
Width (mm): 10.00
Damage Threshold, Reference: 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant