

11.60µm CWL, 25.0mm Diameter, 0.50µm FWHM, IR Bandpass Filter



Stock #25-722 3-5 DAYS

-

1

+

A\$955.20

ADD TO CART

Qty 1-9
A\$955.20
Qty 10+
A\$859.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 ±0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):
22.0

Center Wavelength CWL (nm): 11,600.00 ±40
Full Width-Half Max FWHM (nm): 500.00 ±50
Substrate: ☐ Germanium
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 80 (minimum)
Type: Bandpass Filter
Typical Applications: Astronomical Mapping
Blocking Wavelength Range (nm): 200 - 14500
Center Wavelength CWL (μm): 11.60 ±0.04
Full Width-Half Max FWHM (μm): 0.50 ±0.05

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant