

1.1mW 635nm 30°, VLM™2 Laser Line Focusable



Stock #52-896 2 In Stock

-

1

+

A\$473^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	A\$473.60 each
Need More?	Request Quote

Product Downloads



General

Type of Laser:	
Diode	
Laser Class - CDRH:	
IIIa	

Physical & Mechanical Properties

Weight (g):	
28.00	
Diameter (inches):	
0.58	
Length (inches):	

1.82	
Optical Properties	
635.00	Wavelength (nm):
1.00	Beam Width (mm):
Red	Color:
30.00	Fan Angle (°):
Focus Range (mm): Face of module to past collimation	

Electrical	
50/70 (Typical/Maximum)	Operating Current (mA):
1.1	Output Power (mW):
±4	Output Power Tolerance (%):

Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately. USA: #59-099 Europe: #35-201 Japan: #59-099 Korea: #33-771 China: #59-099	
5-10 DC	Output Voltage (V):
Free Space	Output Type:

Environmental & Durability Factors	
-10 to +40	Operating Temperature (°C):

Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Bright 635nm Beam, 1.1mW and 1.4mW Models
- Non-Rotating Optics
- Non-Intrusive Built-in Focusing Mechanism
- Recommended Power Supply: [#59-099](#)

By combining the robust package of our popular [Visible Laser Modules \(VLM™\)](#) with the convenience of focusing, the VLM™ 2 Focusable Laser Modules offer a dramatic increase in line definition at variable working distances. These focusing laser modules are ideal for machine vision, medical diagnostics and manufacturing applications. All have a locking knurled outer ring to keep the beam at desired focus. Additional features include: green on/off LED, 24" leads, fully shielded drive circuitry and reverse polarity protection. ESD Class 2 protection to ML-STD-1686C and CDRH certified. [Power Supply](#), required for operation, sold separately.

Technical Information



