

TECHSPEC® 10X, 532nm Draconis® Nd:YAG Laser Line Beam Expander



TECHSPEC® Draconis™ Nd:YAG Laser Line Beam Expanders

Stock #59-127 3-5 DAYS

⊖ 1 ⊕

A\$1,465.60

ADD TO CART

Qty 1-4
A\$1,465.60
Qty 5+
A\$1,296.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm):
532

Entrance Aperture (mm): 8
Exit Aperture (mm): 33
Expansion Power: 10X
Focus Range: 1.5m - ∞
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 98.00
Mounting Threads: Input: Male C-Thread (1" x 32 TPI) Output: Male T2-Thread (M42 x 0.75)
Type: Beam Expander
Weight (g): 149
Housing Diameter (mm): 46
Transmitted Wavefront, P-V: λ/10 @ 1mm Input Beam, λ/4 @ 3mm Input Beam
Coating Specification: R _{abs} <0.25% @ 531 - 533nm R _{avg} <0.5% @ 510 - 555nm
Wavelength Range (nm): 510 - 555
Style: Fixed Magnification
Divergence Adjustment: Non-Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View