

**TECHSPEC® 12.7mm Dia. 266nm 0-45°, Nd:YAG Laser Line Mirror**



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#38-833** **2 In Stock**

- 1 + A\$256.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	A\$256.00 each
Qty 6-25	A\$227.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

**Back Surface:**

Commercial Polish

12.70 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.20 **Thickness (mm):**

## Optical Properties

10-5 **Surface Quality:**

99.8 **Reflection at DWL (%):**

$R_{\text{abs}} >99.8\%$  @ 266nm **Coating Specification:**

263 - 268 **Wavelength Range (nm):**

$\lambda/10$  **Surface Flatness (P-V):**

Dielectric **Coating Type:**

Laser Mirror (266nm) **Coating:**

266 **Design Wavelength DWL (nm):**

0-45 **Angle of Incidence (°):**

[Fused Silica](#) (Corning 7980) **Substrate:**

2 J/cm<sup>2</sup> @ 266nm, 20ns, 20Hz **Damage Threshold, Reference:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

**Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts