

[See all 4 Products in Family](#)

11" x 11", 0.085" FL, Lenticular Array



Stock **#43-028** 7 In Stock

-

1

+

A\$232^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	A\$232.00 each
Qty 11-49	A\$209.60 each
Need More?	Request Quote

Product Downloads

General	
Type:	Lens Array
Number of Lenses:	64 per 25.4mm
Physical & Mechanical Properties	
Center Thickness CT (inches):	0.09
Center Thickness CT (mm):	2.20

±0.05	Dimensional Tolerance (inches):
11 x 11	Dimensions (inches):
279.4 x 279.4	Dimensions (mm):
11 x 11	Effective Size (inches):

±40	Thickness Tolerance (%):
±0.88	Thickness Tolerance (mm):

Optical Properties

2.16	Effective Focal Length EFL (mm):
Acrylic	Substrate: ☐
Uncoated	Coating:
400 - 1100	Wavelength Range (nm):

0.09	Effective Focal Length EFL (inches):
1.49	Index of Refraction (n _d):

Environmental & Durability Factors

80 (Maximum)	Operating Temperature (°C):
--------------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Arrays of Conventional Cylinder Lenses
- Used as High-Efficiency Diffusers
- Cylindrical Axis of Lenslet is Aligned Along the First Dimension

Lenticular Arrays consist of an array of conventional cylindrical lenses which efficiently divide, focus, and diffuse light rays. The focal length of each cylindrical lenslet is typically 3 to 5 times its width and its axis is aligned along the first dimension specified under array dimensions. Lenticular Arrays are ideal for use as high-efficiency diffusers within short working distances, projection screens and stereoscopic (3D) photography.

Technical Information



