

12 x 12mm, 800µm Pitch, 1.7° Divergence, Double Sided Cyl. Lens Array



Stock #23-874 3-5 DAYS

⊖ 1 ⊕

A\$1,104.00

ADD TO CART

Qty 1-10
A\$1,104.00
Qty 11+
A\$992.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
24.70 @ 1064nm

Substrate: [Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:
Lens Array (Two Sided)

Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.1
Dimensions (mm): 12.0 x 12.0
Divergence Angle (°): 1.7 (Full Width)
Pitch (µm): 800
Radius R (mm): 11.100
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View