

Richardson Gratings™ 1200 Grooves, 12.5 x 12.5mm, 900nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock **#37-127** 3-5 DAYS

- 1 +

A\$209.60

ADD TO CART

Qty 1+

A\$209.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
500 - 1500

Blaze Wavelength (nm): 900 ±25
Blaze Angle (°): 32.7
Peak Efficiency, Typical (%): 94
Dimensions (mm): 12.5 x 12.5 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 12.50
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.50
Reflected Wavefront, RMS: $\lambda/4$
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S, P and Average
Master Reference: MR224
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View