

[See all 2 Products in Family](#)

125° Diffusing Angle, 5mm Sq., Wide Angle Diffuser



Wide Angle Diffusers

Stock **#23-877** **2 In Stock**

-

1

+

A\$612⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$612.80 each
Qty 11-25	A\$550.40 each
Qty 26-49	A\$520.00 each
Need More?	Request Quote

Product Downloads

General

Type:

Flat Top Diffuser

Note:

Recommended $M^2 > 10$ and beam size $> 2.5\text{mm}$
FW e^2 for best homogeneity and steep slopes

Physical & Mechanical Properties

Clear Aperture CA (mm):

4.5 x4.5	
5.00 x5.00 ±0.1	Dimensions (mm):
0.50 ±0.05	Thickness (mm):
Optical Properties	
125	Diffusing Angle (°):
Uncoated	Coating:
S-TIH53	Substrate: □
90	Transmission (%):
1064	Design Wavelength DWL (nm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- 25 and 125° Diffusing Angles Available
- 90% Transmission Efficiency
- Eye-Safe ROE, No Zero-Order and No Hot Spot

Wide Angle Diffusers are used to create diffused top hat beam profiles in one dimension and are available in angles of 25 or 125°. These diffusers can be easily paired for diffusion in two dimensions for square or rectangular output profiles with a steep edge slope and high homogeneity. These diffusers have increased transmission efficiency and uniformity versus standard ground glass diffusers. Wide Angle Diffusers are an eye-safe refractive optical element (ROE) with no zero-order and no hot spots. These diffusers are ideal for integration into LIDAR, heads up displays (HUDs), time of flight, 3D sensing, and machine vision applications.

Note: These are designed for use with collimated light with a minimum beam size of 2.5mm FWH/e². Use with diverging beams or beam arrays will change output profiles.