

TECHSPEC®

12.5 x 12.5mm Wire Grid Polarizing Film



TECHSPEC® Wre Grid Polarizing Film

Stock **#34-251** CLEARANCE 3-5 DAYS

- 1 +

A\$49.52

ADD TO CART

Qty 1+

A\$49.52

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0 - 45

Extinction Ratio:
>4,250:1 @550nm

Substrate: [Aluminum Wires on TAC Film](#)

Length (mm):
12.50

Operating Temperature (°C): 60 Max @ 90% RH 105 in dry conditions
Dimensions (mm): 12.5 x 12.5
Thickness (mm): 0.08
Transmission (%): 85 (for p-polarized light @ 550nm)
Type: Linear Polarizer
Dimensional Tolerance (mm): +0/-0.3
Construction: Wire Grid
Wavelength Range (nm): 400 - 1200
Width (mm): 12.50
Axis Orientation: 0° ± 1.5°, marked by Notch

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)