

**TECHSPEC® 12.0mm Diameter x -15 FL, NIR I Coated, Plano-Concave Lens**

Stock #49-526 20+ In Stock

 [Other Coating Options](#)   **A\$77.20****ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | <b>A\$77.20</b> each          |
| Qty 10-25      | <b>A\$69.20</b> each          |
| Qty 26-49      | <b>A\$61.60</b> each          |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**SPECIFICATIONS****General**

Type:

## Physical & Mechanical Properties

|                      |   |
|----------------------|---|
|                      | <b>Diameter (mm):</b>                   |
| 12.00 +0.0/-0.025    |   |
|                      | <b>Bevel:</b>                           |
| Protective as needed |   |
| 3.00                 | <b>Center Thickness CT (mm):</b>        |
| ±0.05                | <b>Center Thickness Tolerance (mm):</b> |
| <1                   | <b>Centering (arcmin):</b>              |
| 11.00                | <b>Clear Aperture CA (mm):</b>          |
| 4.47                 | <b>Edge Thickness ET (mm):</b>          |

## Optical Properties

|  |   |
|--|---|
|  | <b>Effective Focal Length EFL (mm):</b>   |
| -15.00                                     |   |
|  | <b>Substrate:</b> <input checked="" type="checkbox"/> <a href="#">N-SP11</a>                                  |
| 1.25                                       | <b>f#:</b>  |
| 0.40                                       | <b>Numerical Aperture NA:</b>   |
|  | <b>Coating:</b>   |
| NIR I (600-1050nm)                         |   |
| 600 - 1050                                 | <b>Wavelength Range (nm):</b>   |
| -16.68                                     | <b>Back Focal Length BFL (mm):</b>  |
|  | <b>Coating Specification:</b>   |
| $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$ |   |
| 587.6                                      | <b>Focal Length Specification Wavelength (nm):</b>  |
| ±1   | <b>Focal Length Tolerance (%):</b>  |
| -11.77                                     | <b>Radius R<sub>1</sub> (mm):</b>   |
| 40-20                                      | <b>Surface Quality:</b>   |
|  | <b>Damage Threshold, By Design:</b> <input checked="" type="checkbox"/><br>7 J/cm <sup>2</sup> @ 1064nm, 10ns |
| 1.5λ                                       | <b>Power (P-V) @ 632.8nm:</b>   |
| N4   | <b>Irregularity (P-V) @ 632.8nm:</b>  |

## Regulatory Compliance


|                                    |
|------------------------------------|
| <b>RoHS 2015:</b>                  |
| <a href="#">Compliant</a>          |
| <b>Certificate of Conformance:</b> |
| <a href="#">View</a>               |
| <b>Reach 235:</b>                  |
| <a href="#">Compliant</a>          |

## PRODUCT DETAILS

- AR Coated to Provide <0.5% Reflectance per Surface for 600 - 1050nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), and [NIR II](#)


TECHSPEC® NIR I Coated Plano-Concave (PCV) Lenses are designed to bend parallel input rays to diverge from one another on the output side of the lens causing this lens to have a negative focal length. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Plano-Concave (PCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® NIR I Coated Plano-Concave (PCV) Lenses offer optimal performance in the 600nm to 1050nm range. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), or with [NIR II](#) AR coating options.

## TECHNICAL INFORMATION



N-BK7


### Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV- NIR spectra.

[Click Here to Download Data](#)

### N-BK7 with $\text{MgF}_2$ Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with  $\text{MgF}_2$  (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{avg}} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{avg}} \leq 0.5\% @ 350 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.


[Click Here to Download Data](#)

### N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength




The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 880\text{nm}$   
 $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$   
 $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 532\text{nm}$   
 $R_{abs} \leq 0.25\% @ 1064\text{nm}$   
 $R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$   
 $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$   
 $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## COMPATIBLE MOUNTS