

TECHSPEC[®] 12.5mm Dia 0.63 NA, NIR Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#87-991** 3-5 DAYS

[Other Coating Options](#)

− 1 +

A\$632.00

ADD TO CART

Qty 1-5

A\$632.00

Qty 6+

A\$505.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Effective Focal Length EFL (mm):

10.00 @ 587.6nm
Numerical Aperture NA: 0.63
Back Focal Length BFL (mm): 4.52
Substrate: Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: NIR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 11
Edge Thickness ET (mm): 2.03
Center Thickness CT (mm): 8.00 ±0.1
f/#: 0.79
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant