

TECHSPEC® 12.5mm Dia. 1064nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock **#88-532** 3-5 DAYS

1

A\$230.40

ADD TO CART

Qty 1-5

A\$230.40

Qty 6+

A\$203.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mrror

Parallelism (arcmin):

<3
Clear Aperture (%)>90
Back Surface:Ground
Reflection at DWL (%)99.9
Coating Specification:R_{abs} >99.8% @ 1064nm
Surface Flatness (P-V):λ/10
Coating Type:Dielectric
Coating:Laser Mirror (1064nm)
Design Wavelength DWL (nm):1064
Diameter (mm):12.50 +0.0/-0.2
Thickness (mm):6.00 ±0.2
Angle of Incidence (°):0-45
Substrate: Fused Silica (Coming 7980)
Damage Threshold, Reference: 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View