


TECHSPEC[®] 12.5mm Dia., 1mm Thick, MgF₂ Coated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock #17-173 8 In Stock

-

1

+

A\$66⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$66.40 each
Qty 6-25	A\$54.40 each
Qty 26-99	A\$49.60 each
Need More?	Request Quote

Product Downloads

General	
Protective Window	Type:
Physical & Mechanical Properties	
Protective as needed	Bevel:
11.25	Clear Aperture CA (mm):

12.50 +0.00/-0.25	Diameter (mm):
1.00 ±0.10	Thickness (mm):
Fine Ground	Edges:
500.00	Knoop Hardness (kg/mm ²):
0.22	Poisson's Ratio:
71.5	Young's Modulus (GPa):

Optical Properties	
58.3	Abbe Number (v _d):
MgF ₂ (632.8nm)	Coating:
R _{avg} ≤1.50% @632.8nm (N-BK7)	Coating Specification:
1.523	Index of Refraction (n _d):
B270	Substrate:
1λ	Surface Flatness (P-V):
60-40	Surface Quality:
400 - 700	Wavelength Range (nm):
10 J/cm ² @ 532nm, 10ns	Damage Threshold, By Design: ☐


Material Properties	
9.4 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.56	Density (g/cm ³):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Large Selection of Sizes
 - Available Uncoated, MgF2, or VIS-NIR Anti-Reflection (AR) Coated
 - Custom Sizes Available for Volume OEM Requirements
- TECHSPEC® B270 Windows offer a high transmission from the visible to the near-infrared (NIR). They have a similar refractive index to N-BK7 while being more cost-effective. These windows are often used as a protective element due to their high solarization stability and chemical resistance, making them ideal for standard window applications. TECHSPEC® B270 Windows are available either uncoated or coated with a MgF2 or VIS-NIR Anti-Reflection (AR) Coating. Both circular and square options are offered in various sizes, and custom sizes and coatings are available for OEM applications.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
