

[See all 97 Products in Family](#)

## TECHSPEC® 12.5mm FL f/2.5, Blue Series IR-Cut M12 Lens



Stock #24-458 **16 In Stock**

⊖ 1 ⊕ A\$136<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-49	A\$136.00 each
Qty 50+	A\$108.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Blue Series	<b>Product Family:</b>
M12 Imaging Lens	<b>Type:</b>
Yes	<b>IR Cut Filter:</b>
	<b>Special Type of Lens:</b>

## Physical & Mechanical Properties

Fixed	<b>Iris Option:</b>
22.90	<b>Length (mm):</b>
15	<b>Maximum Diameter (mm):</b>
15	<b>Outer Diameter (mm):</b>
5	<b>Weight (g):</b>

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
28.9°

**Field of View at Max Sensor Format:**  
Horizontal: 78.1mm - 28.9°  
Vertical: 58.5mm - 21.8°  
Diagonal: 97.7mm - 35.7°

**Horizontal Field of View, 1.2" Sensor:**  
78.0mm - 28.8°

**Horizontal Field of View, 1/2.5" Sensor:**  
70.6mm - 26.2°

**Horizontal Field of View, 1/3" Sensor:**  
58.4mm - 21.8°

**Horizontal Field of View, 1/4" Sensor:**  
43.8mm - 16.4°

**Maximum Image Circle (mm):**  
8.00

**Numerical Aperture NA, Object Side:**  
0.0151

**Number of Elements (Groups):**  
5(5)

**Wavelength Range (nm):**  
400 - 700

**Focal Length FL (mm):**  
12.50

**Working Distance (mm):**  
150 - ∞

**Aperture (f/#):**  
f/2.5

**Distortion (%):**  
-0.36 @ Full Field

**Back Focal Length BFL (mm):**  
10.1 - 9.7

**Coating Specification:**  
M4 MgF<sub>2</sub> @ 550nm

**Entrance Pupil Position (mm):**  
10.87

**Object Space Principal Plane (mm):**  
10.14

**Image Space Principal Plane (mm):**  
-3.01

**Maximum Distortion (%):**  
-0.36

**Exit Pupil Position (mm):**  
-2.33

**Lens Wavelength Range:**  
VIS (IR-Cut Filter)

## Sensor

1/2"	<b>Maximum Sensor Format:</b>
1.40	<b>Pixel Size (µm):</b>

## Threading & Mounting

N/A	<b>Filter Thread:</b>
S-Mount (M12 x 0.5)	<b>Mount:</b>

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- [Ruggedized Designs](#) Also Available

TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our [TECHSPEC® Green Series M12 Lenses](#). Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x0.5 Adapter for C-Mount Cameras ([#53-675](#)) or the M12 x0.5 C-Mount Adapter with Rubber O-Ring ([#59-241](#)) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a [Request for Prescription Form](#).

**Note:** Compatible [TECHSPEC® M12 Imaging Lens Accessories](#) available.

Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- Blue Series M12 Lenses: High resolution finite conjugate designs optimized for machine vision working distances.
- [Rugged Blue Series M12 Lenses: Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- [Green Series M12 Lenses:](#) Finite conjugate designs optimized for machine vision working distances.
- [Red Series M12 Lenses:](#) Infinite conjugate designs optimized for high resolution performance out to infinity.
- [HEO Series M12 Lenses:](#) Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- [Liquid Lens M12 Lenses:](#) Integrated liquid lens for fast electronic focus.

## Technical Information

Focal Length	A	B	C*	D
2.0mm	18.0mm	21.7mm	2.26mm	4.75mm
3.0mm	14.0mm	17.1mm	4.8 - 4.7mm	5.8mm
4.0mm	14.0mm	19.7mm	6.1 - 6.0mm	4.4mm
5.0mm	14.0mm	14.6mm	4.0 - 3.9mm	3.7mm
6.0mm	14.0mm	14.1mm	6.9 - 6.8mm	4.5mm
8.0mm	14.0mm	12.3mm	8.8 - 8.6mm	3.7mm
10.0mm	14.0mm	17.0mm	6.6 - 6.3mm	3.7mm
12.5mm	15.0mm	22.9mm	10.1 - 9.7mm	4.8mm
17.5mm	14.0mm	20.7mm	5.8 - 4.9mm	7.6mm
25.0mm	18.0mm	30.0mm	8.5 - 6.5mm	11.5mm
35.0mm	18.0mm	29.5mm	18.72 - 14.0mm	14.5mm



\*Specified for Optimized Working Distance of 150 - 250mm.