

TECHSPEC® 12.5mm Dia. x 75mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-669-INK** 3-5 DAYS

[Other Coating Options](#)



1



A\$145.60

ADD TO CART

Qty 1-5
A\$145.60
Qty 6+
A\$116.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):
75.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 72.35
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 4.60 ±0.10
Center Thickness CT 1 (mm): 3.00 ±0.05
Center Thickness CT 2 (mm): 1.60 ±0.05
Radius R₁ (mm): 46.44
Radius R₂ (mm): -33.77
Radius R₃ (mm): -95.94
Edge Thickness ET (mm): 3.97
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 6.00
Numerical Aperture NA: 0.08
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View