


[See all 2 Products in Family](#)

**TECHSPEC® 12.7 x 50.8mm EFL 90° Uncoated Glass Off-Axis Parabolic Mirror**



High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors



Stock **#18-658** **20+ In Stock**

⊖ 1 ⊕ **A\$1,318<sup>40</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>A\$1,318.40</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Off-Axis Parabolic Mirror **Type:**

**Physical & Mechanical Properties**

12.70 +0/-0.10 **Diameter (mm):**

<10 RMS **Surface Roughness (□):**

90 Clear Aperture (%):

90

Y Offset (mm):

50.80

## Optical Properties

Effective Focal Length EFL (mm):

50.80

Focal Length Tolerance (%):

±1

Coating:

Uncoated

Off-Set Angle (°):

90

Parent Focal Length PFL (mm):

25.4

Surface Figure, RMS:

λ/8 @ 632.8nm

Surface Quality:

40-20

Substrate:

[UV Fused Silica](#)

Reflected Wavefront, RMS:

λ/4 @ 632.8nm

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- High Quality Fused Silica Substrate
- <10Å Surface Roughness for Low Scatter
- 90° Offset Angle for Easy Integration

TECHSPEC® High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors feature a surface roughness of less than 10Å which is the lowest scatter available in an off-the-shelf solution. Featuring a fused silica substrate, these low scatter alternatives perform better in the UV wavelength range than traditional metallic substrate OAPs. TECHSPEC® High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors are ideal for Schlieren, MTF, and Czerny-Turner and Litrow spectrometer systems due to their low scattering.

**Note:** Uncoated options require a coating for use. Contact us for a custom coating quote for your specific wavelength.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).