

TECHSPEC® 12.5mm Dia. x 90mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-332** 3-5 DAYS
[Other Coating Options](#)

- 1 + **A\$137.60**

ADD TO CART

Qty 1-5
A\$137.60
Qty 6+
A\$110.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):
90.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 88.47
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 3.58 ±0.10
Center Thickness CT 1 (mm) : 1.98 ±0.05
Center Thickness CT 2 (mm) : 1.60 ±0.05
Radius R₁ (mm) : 55.80
Radius R₂ (mm) : -40.17
Radius R₃ (mm) : -116.32
Edge Thickness ET (mm) : 3.06
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 7.2
Numerical Aperture NA : 0.07
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View