

TECHSPEC® S-Mount, 12.5mm Cube Mount



12.5mm x 17.5mm Plate S-Mount Holder



Stock #11-139 **1 In Stock**

⊖ 1 ⊕ A\$444⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$444.80 each
Qty 5-9	A\$416.00 each
Qty 10-25	A\$395.84 each
Need More?	Request Quote

Product Downloads

General

Function:
Optic Mount (Fixed)

Type of Optics:
Cube

Note:
Includes one S-Mount Aperture Cap ([# 11-137](#))

Dimensions of Compatible Optics (mm):

12.5 Sq.

Physical & Mechanical Properties

Dimensions (mm):

25.4 x 25.4 x 34.3

Extension Length (mm):

25.4

Min. Thickness of Compatible Optics (mm):

12.5

Max. Thickness of Compatible Optics (mm):

12.5

Threading & Mounting

Thread Type:

S-Mount

Compatible Post:

1/4-20

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

