

[See all 13 Products in Family](#)

TECHSPEC®

S-Mount, 12.5mm Cube Mount



12.5mm x 17.5mm Plate S-Mount Holder



Stock #11-139 1 In Stock

-

1

+

A\$444⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$444.80 each
Qty 5-9	A\$416.00 each
Qty 10-25	A\$395.84 each
Need More?	Request Quote

Product Downloads

General

Function:

Optic Mount (Fixed)

Type of Optics:

Cube

Note:

Includes one S-Mount Aperture Cap ([# 11-137](#))

Dimensions of Compatible Optics (mm):	
12.5 Sq.	
Physical & Mechanical Properties	
Dimensions (mm):	
25.4 x 25.4 x 34.3	
Extension Length (mm):	
25.4	
Min. Thickness of Compatible Optics (mm):	
12.5	
Max. Thickness of Compatible Optics (mm):	
12.5	
Threading & Mounting	
Thread Type:	
S-Mount	
Compatible Post:	
1/4-20	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

