

TECHSPEC<sup>®</sup>

12.5mm H x 25mm L x -12.5mm FL MgF<sub>2</sub> Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC<sup>®</sup> Illumination Grade PCV Cylinder Lenses

Stock **#68-069** **8 In Stock**

-

1

+

A\$126<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | A\$126.00 each                |
| Qty 6-25       | A\$114.00 each                |
| Qty 26-49      | A\$108.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Cylinder Lens, Plano-Concave

Type:

Physical & Mechanical Properties

2.50

Center Thickness CT (mm):

Center Thickness Tolerance (mm):

|             |                             |
|-------------|-----------------------------|
| ±0.1        |                             |
| +0.0/-0.2   | Dimensional Tolerance (mm): |
| 12.5 x 25.0 | Dimensions (mm):            |
| 4.51        | Edge Thickness ET (mm):     |

Optical Properties

|                                       |                                                       |
|---------------------------------------|-------------------------------------------------------|
| -12.50                                | Effective Focal Length EFL (mm):                      |
| N-SF11                                | Substrate: <input type="checkbox"/>                   |
| MgF <sub>2</sub> (400-700nm)          | Coating:                                              |
| 400 - 700                             | Wavelength Range (nm):                                |
| -13.9                                 | Back Focal Length BFL (mm):                           |
| R <sub>avg</sub> ≤1.75% @ 400 - 700nm | Coating Specification:                                |
| ±3                                    | Focal Length Tolerance (%):                           |
| -9.81                                 | Radius R <sub>1</sub> (mm):                           |
| 60-40                                 | Surface Quality:                                      |
| 10 J/cm <sup>2</sup> @ 532nm, 10ns    | Damage Threshold, By Design: <input type="checkbox"/> |


Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 235:                  |

## Product Details

- Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence
  - Circular and Rectangular Form Factors
  - Multiple Coating Options Available
- TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.
- The thin lens approximation for the length of a line generated by a negative cylinder lens is:  $L = 2 * (r_0/f) * (z + f)$  where L is the line length,  $r_0$  is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

## Technical Information



## Coating Curves

## Custom

- Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.
- Our capabilities include:
- Custom dimensions, materials, coatings, and more
  - High-precision surface quality and flatness

- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---