

[See all 44 Products in Family](#)

TECHSPEC® 12.7mm Dia., 532 & 1064nm T, 355nm R 45° Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock **#38-779** **2 In Stock**

A\$361⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$361.60 each
Qty 6-24	A\$324.80 each
Qty 25-49	A\$289.60 each
Need More?	Request Quote

Product Downloads

General

Harmonic Beamsplitter **Type:**

Physical & Mechanical Properties

>85 **Clear Aperture (%):**

Dichroic **Construction:**

12.70 +0.00/-0.10	Diameter (mm):
<3	Parallelism (arcmin):

6.35 ±0.20	Thickness (mm):
------------	------------------------

Optical Properties

45	Angle of Incidence (°):
----	--------------------------------

Coating Specification:	
Surface 1: R _{abs} : >99% @ 355nm, T _{abs} : >95% @ 532, 1064nm	
Surface 2: R _{abs} : <0.75% @ 532, 1064nm	

355	Reflection Wavelength (nm):
-----	------------------------------------

Fused Silica (Coming 7980)	Substrate: <input type="checkbox"/>
-----------------------------------	--

M10	Surface Flatness (P-V):
-----	--------------------------------

10-5	Surface Quality:
------	-------------------------

532, 1064	Transmission Wavelength (nm):
-----------	--------------------------------------

Damage Threshold, By Design: <input type="checkbox"/>	
Surface 1:	
2.5 J/cm ² @ 355nm, 20ns, 20Hz	
5 J/cm ² @ 532nm, 20ns, 20Hz	
7.5 J/cm ² @ 1064nm, 20ns, 20Hz	
Surface 2:	
15 J/cm ² @ 1064nm, 20ns, 20Hz	
10 J/cm ² @ 532nm, 20ns, 20Hz	

Regulatory Compliance

Compliant	RoHS 2015:
------------------	-------------------

Compliant	Reach 209:
------------------	-------------------

View	Certificate of Conformance:
-------------	------------------------------------

Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- M10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

Note: The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.

Compatible Mounts