

TECHSPEC[®] 12.7mm Dia., 6.35mm Thick, Superpolished Laser Window Substrate



TECHSPEC[®] Superpolished Substrates

Stock #11-554 13 In Stock

-

1

+

A\$579²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$579.20 each
Qty 11-25	A\$510.40 each
Qty 26+	A\$449.60 each
Need More?	Request Quote

Product Downloads

General	
Laser Window Substrate	Type:
Physical & Mechanical Properties	
6.35 ±0.10	Thickness (mm):
11.43	Clear Aperture CA (mm):

12.70 +0.00/-0.10	Diameter (mm):
90	Clear Aperture (%):
<30	Parallelism (arcsec):
Protective as needed	Bevel:
Surface Roughness (□): ≤1 RMS as measured using an optical profiler using a 20x objective at a spatial frequency bandwidth of 9 to 250 cycles per mm	
Commercial Polish	Edges:

Optical Properties

Fused Silica (Corning 7980)	Substrate: □
1.458	Index of Refraction (n _d):
10-5	Surface Quality:
Uncoated	Coating:
67.8	Abbe Number (v _d):
200 - 2200	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Superpolished on Both Surfaces with ≤1Å RMS Surface Roughness
- Low Scatter Surfaces Ideal for UV or High Power Laser Applications
- UV Fused Silica Substrates with Polished Bevels and Edges
- [In-House Manufacturing](#) Enables Custom Sizes and Shapes from 6 to 76.2mm and Surface Roughness <0.5Å

TECHSPEC® Superpolished Substrates are superpolished on both surfaces to achieve superior surface specifications, including ≤1Å RMS surface roughness. The superpolished surfaces of these windows reduce scatter, making them ideal for UV or high power laser applications where scatter is a concern. The low scatter of these windows also allows for their use as substrates for ion-beam sputtering (IBS) coatings. TECHSPEC Superpolished Substrates are used in metrology applications including cavity-ring down spectroscopy, scatterometry, and in ring laser gyroscopes, as well as in UV medical applications such as eye surgery. Please [contact us](#) if your application requires a Superpolished Substrate with a custom size, if you are interested in [custom coating opportunities](#), or to discuss how these low scatter substrates will affect your coated optic performance. Single side superpolishing is also available.

Superpolished Optics for Minimized Scatter

LEARN MORE □

Compatible Mounts