


TECHSPEC[®] 12.5mm Square Uncoated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock #64-085 3-5 DAYS



1



A\$48.80

ADD TO CART

Qty 1-5

A\$48.80

Qty 6+

A\$39.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):
58.3

Bevel:
Protective as needed

Clear Aperture CA (mm):
11.25 x 11.25

Dimensions (mm): 12.50 x 12.50
Thickness (mm): 2.00
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 9.4 (+20 to +300°C)
Density (g/cm³): 2.56
Edges: Fine Ground
Index of Refraction n_d: 1.523
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.22
Substrate: B270
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 360 - 2700
Young's Modulus (GPa): 71.5
Length (mm): 12.50
Width (mm): 12.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant