

TECHSPEC® 12.7mm Dia. x 125mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#69-922-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$145.60**

ADD TO CART

Qty 1-5
A\$145.60
Qty 6+
A\$116.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.70 ±0.025

Effective Focal Length EFL (mm):
125.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 121.95
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.43
Centering (arcmin) : <1
Center Thickness CT (mm) : 6.50 ±0.20
Center Thickness CT 1 (mm) : 4.50 ±0.10
Center Thickness CT 2 (mm) : 2.00 ±0.10
Radius R₁ (mm) : 76.92
Radius R₂ (mm) : -55.48
Radius R₃ (mm) : -162.59
Edge Thickness ET (mm) : 6.11
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 9.84
Numerical Aperture NA : 0.05
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View