

12.7mm Dia. 532nm $\lambda/2$ Quartz Waveplate Multiple Order



Stock #85-084 3-5 DAYS

- 1 + **A\$411.20**

ADD TO CART

Qty 1-5
A\$411.20
Qty 6+
A\$332.80
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 8.00
Coating: Laser V-Coat (532nm)
Design Wavelength DWL (nm): 532
Diameter (mm): 12.70 +0.00/-0.25

Substrate: Crystal Quartz
Retardance: λ/2
Surface Quality: 10-5
Thickness (mm): 6.40 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0015
Retardance Order: Multiple Order

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View